

Quantec Corridor Display

Part No. OT608C



Overview

- A 16 character x 2 line display used to indicate incoming calls in corridors, staff rooms, nursing stations, etc.
- Includes an onboard sounder and buttons to accept, scroll through and manually divert calls.
- Shows call type, call location and (depending on the device used to make the call) the User ID or name of the person calling.
- Highest priority calls are shown first with a message saying how many calls are waiting.
- Flash and sounder rates intensify to reflect the urgency of incoming calls.
- Adjustable contrast and volume controls.
- External sounder connection.



More Information

Technical Specifications

Power requirements Nominal 24V DC (from Quantec Controller/Network)

Quiescent current 5mA (with back light off).

Indicators 2 line x 16 character backlit LCD display.

Accept (A); Scroll Up; Scroll Down. Adjust contrast; Adjust volume; Enable internal/external beeper. Controls

Connections

External sounder connection (current sink to the NET- line rated at 30 V, 30mA, 300 mW dissipation max.) **Expansion connections**

Onboard Sounder Yes.



T 01942 322744

E sales@c-tec.co.uk

C-TEC, Challenge Way, Martland Park, Wigan, WN5 0LD United Kingdom



















Onboard Infrared Receiver No.

Product dimensions (mm) $146\ W\ x\ 87\ H\ x\ 35\ D$ mm. Mount on a 35mm deep back box.

Construction & finish Plastic. IP Rating IP40. Weight 166g.

Operating conditions/temperature -5 $^{\circ}$ C to +40 $^{\circ}$ C. Max relative humidity: 95%.

















